


1/4-14 x 7/8 LAPTEK W/ WASHER
[FASTENER #4A] @ 20" O.C.
BETWEEN SUPPORTS



HORIZONTAL REVERSE ROLLED 7.2 FASTENER SPACING
@ PANEL ENDS & INTERMEDIATE SUPPORTS

NOTE:
MBCI RECOMMENDS THAT A REVERSE ROLLED 7.2
PANEL BE USED IN HORIZONTAL APPLICATIONS
SO THAT THE LAP FASTENERS CAN BE INSTALLED
IN THE LOW RIBS.